



Powering Business Worldwide

145-BOX

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664481000

Brand Name: Eaton
Sub Brand: EATON
Type: Duplex, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Surface mount & power
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 15 Amp
Voltage Rating: 250 Vac
Material: Heavy Duty Plastic Construction
Color: Ivory
NEMA Rating: 6-15R
Mounting: Wall
Connection: Screw
Size: 1.21X 1.90 X3.60 IN
Environmental Conditions: Wall
Dielectric Strength: 250 vac
Insulation: Nylon Face
Temperature Rating: -20C to 70C (-4F to 158F)

BP145

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664103605

Brand Name: Cooper Wiring Devices
Type: (1) Dimmer, (1) 3 Speed Fan Controller
Voltage Rating: 120 Vac
Amperage Rating: 1.5 Amp
Wattage: 300 W
Load: Incandescent, Halogen
Number Of Poles: 1
Size: 1.63 In Width
Connection: Wire Lead
Operating Temperature: 0 To 40 Deg C



Powering Business Worldwide

145-BOX

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664481000

Brand Name: Eaton
Sub Brand: EATON
Type: Duplex, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Surface mount & power
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 15 Amp
Voltage Rating: 250 Vac
Material: Heavy Duty Plastic Construction
Color: Ivory
NEMA Rating: 6-15R
Mounting: Wall
Connection: Screw
Size: 1.21X 1.90 X3.60 IN
Environmental Conditions: Wall
Dielectric Strength: 250 vac
Insulation: Nylon Face
Temperature Rating: -20C to 70C (-4F to 158F)

BP145

Socket Pigtail Rubber WP 660W600V #14 BK

UPC: 032664103605

Brand Name: Cooper Wiring Devices
Type: (1) Dimmer, (1) 3 Speed Fan Controller
Voltage Rating: 120 Vac
Amperage Rating: 1.5 Amp
Wattage: 300 W
Load: Incandescent, Halogen
Number Of Poles: 1
Size: 1.63 In Width
Connection: Wire Lead
Operating Temperature: 0 To 40 Deg C