

Straight Blade Devices Decorator Combination GFCI Receptacles with SafeLock™ Protection

15A, 125VAC

Pass & Seymour
legrand




Features


- Meets 2003 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Up-down switching.
- 15 Amp single pole switch rated for 1/2 HP motor loads — perfect for bath or kitchen vent fans.
- Trip Indicator Light (red lamp).
- Prevents line-load reversal miswire: If miswired, GFCI cannot be RESET.
- Improved resistance to surge, corrosion and electrical power line noise.
- Nightlight has durable, cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.
- Side or internal screw-pressure-plate back wire with #14 – #10 AWG solid or stranded copper wire.
- Ground screw with a wire guide channel and back wire clamp.
- Line and load terminations supplied backed out and ready-to-wire.
- High-impact resistant thermoplastic construction (switch, face and back only).
- Extra-long strap.
- Two back wire holes per terminal.
- Welding of face to back body provides sealed tamperproof construction.
- Button colors match the device face.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications


- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity




1594-SWTWCC5



1594-2SWTWCC5



1594-NTLWCC6



NEMA
5-15R

Catalog Number	Switch Rating A. VAC	Receptacle Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	UL20 C22.2 No. 111
Single Pole Switch/GFCI							
1594-SWTICC5	15 120	15 125	Ivory	5-15R	•	•	•
1594-SWTWCC5	15 120	15 125	White	5-15R	•	•	•
1594-SWTLACC5	15 120	15 125	Lt. Almond	5-15R	•	•	•
Two Single Pole Switches/GFCI							
1594-2SWTICC5	15 120	15 125	Ivory	5-15R	•	•	•
1594-2SWTWCC5	15 120	15 125	White	5-15R	•	•	•
1594-2SWTLACC5	15 120	15 125	Lt. Almond	5-15R	•	•	•
Nightlight/GFCI							
1594-NTLICC6	15 120	15 125	Ivory	5-15R	•	•	
1594-NTLWCC6	15 120	15 125	White	5-15R	•	•	
1594-NTLLACC6	15 120	15 125	Lt. Almond	5-15R	•	•	

NEW

NEW

NEW

Straight Blade Devices

Decorator Combination GFCI Receptacles