



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1597TRBK Radiant Self Test TR Gfci 15A 125V BK

Pass & Seymour/Legrand

Catalog Number	1597TRBK
Manufacturer	Pass & Seymour/Legrand
Description	15A 125V Self-Test Tamper-Resistant Gfci Black
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	15
connection	Back and side wire
interrupt rating	4 to 6 mA
Material	Thermoplastic
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73

Descriptions

Description	RADIANT SELF TEST TR GFCI 15A 125V BK
extra long description	P&S 1597TRBK RADIANT SLF TST TR GFC
Long Description	15A 125V Self-Test Tamper-Resistant GFCI Black
Product Type	Radiant SLF TST TR Gfci 15A 125V BK
Special Features	Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007048636
Manufacturers Part Number	1597TRBK
UPC	785007048636

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Specification Grade Tamper-Resistant 15A Self-Test Duplex GFCI



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
Operating Temperature	-35°C to +66°C
standard	cULus, UL Listed, FSUL