



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 165YL4A Temflex Vinyl Electrical Tape, YL, 3/4" X 60' *Minnesota Mining (3M)*

Catalog Number	165YL4A
Manufacturer	Minnesota Mining (3M)
Description	3M™ Temflex™ Vinyl Electrical Tape 165, Yellow, 3/4 In X 60 FT (19 MM X 18 M), 100 Rolls/Case
Weight per unit	0.0186 (lbs/each)
Product Category	Tools & Testers

### Features

Adhesive Type	Rubber
Dielectric Strength	1000
Elongation at Break	2
Voltage Rating	600

### Material, Color, and Finish

Backing Material	Polyvinyl Chloride PVC
------------------	------------------------

### Dimensions and Weight

Thickness	6
-----------	---

### Descriptions

Description	TEMFLEX VINYL ELECTRICAL TAPE, YL, 3/4" X 60'
extra long description	3M 7100169490 3M™ Temflex™ Vinyl E
Features	3M™ Temflex™ Vinyl Electrical Tape 165 is a 6-mil thick, multi-purpose vinyl insulating tape available in 10 colors. It is designed to perform in ambient temperatures up to 194°F (90°C). The tape is conformable for cold weather application down to 32°F (0°C). It has excellent resistance to abrasion, moisture, alkalis, acid, copper corrosion and varying weather conditions. The combination of an elastic PVC backing and pressure-sensitive rubber-based adhesive provides electrical and mechanical protection w
Long Description	3M™ Temflex™ Vinyl Electrical Tape 165, Yellow, 3/4 in x 60 ft (19 mm x 18 m), 100 Rolls/Case
Product Type	3M™ Temflex™ Vinyl Electrical Tape 165

### Manufacturer Information

Brand	Temflex
GTIN	00076308925772
Manufacturers Part Number	165YL4A
UPC	076308925772

### Taxonomies, Classifications, and Categories

Category Description	TAPE
----------------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.0186

## Uses, Certifications, and Standards

Application	Insulation
-------------	------------