

# Eaton 1MCB1200R

Catalog Number: 1MCB1200R

Eaton main circuit breaker, 1200A, Aluminum, NEMA 3R, Underground, 65 kAIC, NGS, Three-wire, Single-phase, 120/240V, (4) #4/0 AWG-500 kcmil, Gray



## General specifications

### Product Name

Eaton main circuit breaker

### Catalog Number

1MCB1200R

### UPC

786849053239

### Product Length/Depth

13.8 in

### Product Height

15.25 in

### Product Width

20.2 in

### Product Weight

135 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

## Product specifications

### Amperage Rating

1200 A

### Bus material

Aluminum

### Feed type

Bottom

### Phase

Single-phase

### Voltage rating

120/240 V

### Utility approvals

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

### Enclosure

NEMA 3R

### Interrupt rating

65 kAIC

### Main circuit breaker

NGS

### Number of wires

3

### Wire size

(4) #4/0 AWG-500 kcmil

## Resources

### Brochures

### Specifications and datasheets

[Eaton Specification Sheet - 1MCB1200R](#)