

# Eaton 1MCB1600RBC-600

Catalog Number: 1MCB1600RBC-600

Eaton main circuit breaker, 1600A, Copper, NEMA 3R, Underground, 100 kAIC, RGH, Three-wire, Single-phase, 120/240V, (4) #500-1000 kcmil, With lug landing to accept 2-600M



## General specifications

### Product Name

Eaton main circuit breaker

### Catalog Number

1MCB1600RBC-600

### UPC

782113964843

### Product Length/Depth

18.5 in

### Product Height

57.2 in

### Product Width

25.2 in

### Product Weight

314 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Amperage Rating

1600 A

### Bus material

Copper

### Feed type

Bottom

### Phase

Single-phase

### Voltage rating

120/240 V

### Enclosure

NEMA 3R

### Interrupt rating

100 kAIC

### Accessory/spare part type

Lug landing to accept 2-600M

### Main circuit breaker

RGH

### Number of wires

3

### Wire size

(4) 500-1000 kcmil

## Resources

### Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1MCB1600RBC-600](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)