

# Eaton 1MCB1600RBCA600

Catalog Number: 1MCB1600RBCA600

Eaton main circuit breaker, 1600A, Copper, NEMA 3R, Underground, RGH, Three-wire, Single-phase, 120/240V, (6) #2 AWG-600 kcmil



Photo is representative

## General specifications

### Product Name

Eaton main circuit breaker

### Catalog Number

1MCB1600RBCA600

### UPC

786685960074

### Product Length/Depth

18.13 in

### Product Height

57.13 in

### Product Width

25.13 in

### Product Weight

314 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

## Product specifications

### Amperage Rating

1600 A

### Bus material

Copper

### Feed type

Bottom

### Phase

Single-phase

### Voltage rating

120/240 V

### Enclosure

NEMA 3R

### Main circuit breaker

RGH

### Number of wires

3

### Wire size

(6) #2 AWG-600 kcmil

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - 1MCB1600RBCA600](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton 1MCB1600RBCA600

Catalog Number: 1MCB1600RBCA600

Eaton main circuit breaker, 1600A, Copper, NEMA 3R, Underground, RGH, Three-wire, Single-phase, 120/240V, (6) #2 AWG-600 kcmil



Photo is representative

## General specifications

### Product Name

Eaton main circuit breaker

### Catalog Number

1MCB1600RBCA600

### UPC

786685960074

### Product Length/Depth

18.13 in

### Product Height

57.13 in

### Product Width

25.13 in

### Product Weight

314 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

## Product specifications

### Amperage Rating

1600 A

### Bus material

Copper

### Feed type

Bottom

### Phase

Single-phase

### Voltage rating

120/240 V

### Enclosure

NEMA 3R

### Main circuit breaker

RGH

### Number of wires

3

### Wire size

(6) #2 AWG-600 kcmil

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - 1MCB1600RBCA600](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)