



## SNK Terminal Blocks T&B Catalog Number:

1SNK506410R0000

**UPC Number:**

80432548900

**Status:**

Active

**Description:**

Gray and dark gray feed through fused terminal block with 6 mm spacing, 13 amp UL rated current with screw clamp connection

### Features

Protect your circuits with 5x20 mm fuse terminal blocks compliant with IEC 60947-7-3 standard

Simplify the distribution thanks to the two jumper channels aligned with ZS4 feed-through and ZS4-S-R1 disconnect terminal blocks

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Fuse Holder
Color	Gray-Dark Gray
Mounting	DIN 3
Series	ZS4-SF
Connection Technology	Screw Clamp
UL Wire Range (AWG)	24-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	0.2-4
Rated IEC Wire Range (Stranded) (mm <sup>2</sup> )	0.22-4

### Dimension Information

L x W x H (mm)	70.3 x 6 x 78.8
Spacing (mm)	6
L x W x H (in)	2.77 x .236 x 3.10
Spacing (inches)	0.236

### Specifications

UL Current (Amps)	13
UL Voltage (VAC)	150

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	400
T&B Sold in UOM	Each
T&B Weight Per UOM	0.04 lbs. Each

### Certifications

Approvals	USR, CSA, CE
-----------	--------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321

