



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2006SB Copper Splice Cap Crimp Conn, 18-10 Awg, 1, 000/Bag

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 2006SB  |
| Manufacturer     | Ideal   |
| Description      | Buchanan, Crimp Connector, Splice Cap, Conductor Range: 18 - 10 Awg, 18/2 Awg Min, 12/4 Awg Max, Finish: Zinc-Plated, Tin-Plated Steel Sleeves, Material: Copper Sleeves, Voltage Rating: 600 V |
| Weight per unit  | 0.0020 (lbs/each)   |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                |                |
|----------------|----------------|
| Material       | Copper Sleeves |
| Voltage Rating | 600            |

### Material, Color, and Finish

|        |                                       |
|--------|---------------------------------------|
| Finish | Zinc-Plated, Tin-Plated Steel Sleeves |
|--------|---------------------------------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | COPPER SPLICE CAP CRIMP CONN, 18-10 AWG, 1,000/BAG  |
| extra long description | IDEAL 2006SB SPLICE CAP 10,000 BX   |
| Features               | Designed for making fast, permanent, pressure-type connectionsSolid copper sleeves require less crimping pressure and resistn corrosion in harsh environmentsUL 486S Listed and CSA C22.2 #188 Certified: comply with Federal Specification W-S-61D   |
| Long Description       | Buchanan, Crimp Connector, Splice Cap, Conductor Range: 18 - 10 AWG, 18/2 AWG Min, 12/4 AWG Max, Finish: Zinc-Plated, Tin-Plated Steel Sleeves, Material: Copper Sleeves, Voltage Rating: 600 V   |
| Product Type           | Splice Cap 10, 000 BX   |
| Special Features       | Features: For #18 To #10 AWG Wire; Minimum 2 #18 AWG; Maximum 4 #12 AWG; Use Buchanan C24 Crimp Tool; Designed For Fast, Permanent, Pressure-Type Connections; UL Listed And CSA Certified; Zinc-Plated Or Copper Sleeves Resist Corrosion; Solid Copper Sleeves Require Less Crimping Pressure; Resist Corrosion In Harsh Environments; UL 486C Listed And CSA C22.2 #188 Certified; Comply With Federal Specification W-S-61D |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Buchanan       |
| GTIN                      | 00781789452913 |
| Manufacturers Part Number | 2006SB         |
| UPC                       | 781789452913   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type                 | Splice Cap                             |

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 10000 |
| Weight Per each | 0.002 |

## Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | For Buchanan C24 Crimp Tool And Designed For Fast, Permanent, Pressure-Type Connections |
| standard    | CSA, UL Listed, RoHS  |