Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2011S Copper Splice Cap Crimp Conn, 14-4 Awg, 50/Bag

Ideal

Catalog Number	2011S
Manufacturer	Ideal
Description	Splice Cap, Copper Conductor Material, 600 V Ac, 0.01 LB
Weight per unit	0.2500 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Copper Sleeves
Voltage Rating	600

Material, Color, and Finish

Finish	Zinc-Plated, Tin-Plated Steel Sleeves

Descriptions

Description	COPPER SPLICE CAP CRIMP CONN, 14-4 AWG, 50/BAG
extra long description	IDEAL 2011S SPL CAP, 50PC BAG
Features	Designed for making fast, permanent, pressure-type connectionsSolid copper sleeves require less crimping pressure and resistn corrosion in harsh environmentsUL 486S Listed and CSA C22.2 #188 Certified: comply with Federal Specification W-S-61D

Manufacturer Information

Brand	Buchanan
GTIN	00781789450070
UPC	781789450070

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Splice Cap

Availability

minimum qty	50

Packaging

Carton	50
Package	500
Weight Per each	0.25

Uses, Certifications, and Standards

Application	For Buchanan C24 Crimp Tool And Designed For Fast, Permanent, Pressure-Type Connections
standard	CSA, UL Listed, RoHS