

Ø

#0 A7

© US P

| AI CAT. # | TRADE SIZE | Ø "A" | "B" | "C" | "D" | SIZE H.W. | SIZE EMT |
|-----------|------------|-------|-------|-------|-------|------------|-------------|
| 2000 | #0 | 0.800 | 0.810 | 1.850 | 0.750 | 3/8", 1/2" | 1/2" |
| 2010 | #1 | 1.000 | 0.850 | 2.150 | 0.750 | 3/4" | 3/4" |
| 2020 | #2 | 1.200 | 0.970 | 2.485 | 0.875 | 1" | 1" |
| 2025 | #2.5 / #3 | 1.700 | 1.206 | 3.265 | 0.875 | 1-1/4" | 11/4"-11/2" |
| 2040 | #4 | 1.875 | 1.090 | 3.220 | 1.000 | 1-1/2" | - |
| 2050 | #5 | 2.250 | 1.220 | 4.090 | 1.000 | 2" | 2" |
| 2060 | #6 | 2.875 | 1.150 | 4.820 | 1.250 | 2-1/2" | 2-1/2" |
| 2070 | #7 | 3.500 | 1.160 | 5.180 | 1.250 | 3" | 3" |
| 2080 | #8 | 4.000 | 1.140 | 5.740 | 1.250 | 3-1/2" | 3-1/2" |
| 2090 | #9 | 4.500 | 1.172 | 6.500 | 1.250 | 4" | 4" |