



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2095TRI 20A 125V IV TR GFI Rec

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | 2095TRI   |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Duplex Receptacle, 20 A, 125 @ 60 HZ V Ac, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Screw Connection, Screw Mount, 60 HZ, 1.73 In Width, 4.20 In Height, High Impact Resistant Thermoplastic, Ivory, 0.025 Sec Trip Time, Tamper Resistant, 0.3800 LB |
| Weight per unit  | 0.3800 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro  |

### Descriptions

|                        |                              |
|------------------------|------------------------------|
| Description            | 20A 125V IV TR GFI REC       |
| extra long description | P&S 2095TRI DISC SUB 2097TRI |

### Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007423860         |
| Manufacturers Part Number | 2095TRI                |
| UPC                       | 785007423860           |

### Taxonomies, Classifications, and Categories

|                      |                         |
|----------------------|-------------------------|
| Category Description | Commercial GFCI devices |
|----------------------|-------------------------|

### Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|

### Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 0.38 |

### Uses, Certifications, and Standards

|          |           |
|----------|-----------|
| standard | UL, cULus |
|----------|-----------|