



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2097TRW Radiant Self Test TR Gfci 20A 125V WH

Pass & Seymour/LeGrand

| | |
|------------------|---|
| Catalog Number | 2097TRW |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, White, 0.025 Sec Trip Time, Tamper Resistant, 0.2800 LB |
| Weight per unit | 0.2750 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------------|-----------------------------------|
| actuator | Control Circuit |
| amperage rating | 20 |
| connection | Back and side wire |
| indoor/outdoor | Indoor |
| interrupt rating | 4 to 6 mA |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Outlet Type | Self-Test, Tamper-Resistant, GFCI |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage | 125.0 V |
| Voltage Rating | 125 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|------|
| Length | 1.03 |
| Width | 1.73 |

Descriptions

| | |
|------------------------|---------------------------------------|
| Description | RADIANT SELF TEST TR GFCI 20A 125V WH |
| extra long description | P&S 2097TRW RADIANT SELF TEST TR GF |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007035872 |
| UPC | 785007035872 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Residential GFCI devices |
| Type | Outlet |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 20.0

Packaging

Carton 1

Package 10

Weight Per each 0.275

Uses, Certifications, and Standards

environmental conditions 95% Humidity, UL 94 V2

Operating Temperature -35°C to +66°C

standard UL, cULus