



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



20MR16TFL35CBAB 20W 12V MR16 Constant Color 40 Deg Flood Halogen *Sylvania-Ledvance*

Catalog Number	20MR16TFL35CBAB
Manufacturer	Sylvania-Ledvance
Description	Tungsten Halogen Tru Aim MR16 Titan Axial Filament Uv Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20WATT 12VOLT Flood Beam
Weight per unit	0.0900 (lbs/each)
Product Category	Halogen Reflector Ar, BR, JDR,

Features

average life	4000
Base	GU5.3 Bipin
beam angle	36
dimmable	Yes
Lamp Type	MR16
lumens	300
Shape	MR16
start type	Instant
Voltage	12.00 V
Voltage Rating	12
Wattage	20

Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000

Descriptions

Description	20W 12V MR16 CONSTANT COLOR 40 DEG FLOOD HALOGEN
extra long description	SYL 20MR16TFL35CBAB-12V/58301 20MR1
Long Description	Tungsten Halogen Tru Aim MR16 TITAN Axial Filament UV Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 20Watt 12Volt Flood Beam
Product Type	20MR16TFL35CBAB 12V 20/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135583018
Manufacturers Part Number	20MR16/T/FL35/C(BAB)-12V/58301
UPC	046135583018



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description QUARTZ

Type HALOGEN

Packaging

Carton 20

Weight Per each 0.09

Uses, Certifications, and Standards

Application Medium Screwbase or bi-pin

standard BAB