



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



20T612DCF120 20W 120V T6.5 Double Contact Bayonet Incan Lamp

Ge By Current Lamps

Catalog Number	20T612DCF120
Manufacturer	Ge By Current Lamps
Description	Ge, 20 WTT, 120 V, 90 LM, 0.813 In Diameter, 5.56 In Length, Double Contact Bayonet (BA15D) Base, 5000 HR Average Life
Weight per unit	0.0600 (lbs/each)
Product Category	Incandescent Tubular T Shape L

Features

average life	5000.0
Base	Double Contact Bayonet (BA15d)
lumens	90.0
Voltage Rating	120.0
Wattage	20.0

Material, Color, and Finish

Color	FROST
Finish	Frost

Dimensions and Weight

Diameter	0.813
Length	5.56

Descriptions

Description	20W 120V T6.5 DOUBLE CONTACT BAYONET INCAN LAMP
extra long description	GEL 20T61/2DC/F 34241 INCANDESCENT
Long Description	GE, 20 WTT, 120 V, 90 LM, 0.813 IN Diameter, 5.56 IN Length, Double Contact Bayonet (BA15d) Base, 5000 HR Average Life
Product Type	34241 Incandescent Lamps

Manufacturer Information

Brand	GE Current
GTIN	00043168342414
Manufacturers Part Number	20T61/2DC/F
UPC	043168342414

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
----------------------	--------------

Packaging

Carton	1
Package	60
Weight Per each	0.06

Uses, Certifications, and Standards

Application	STANDARD
-------------	----------