



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2107 120/277V 2000W SPST Conduit Mount Die Cast Zinc

Nsi Industries

Catalog Number	2107
Manufacturer	Nsi Industries
Description	Conduit Mount, 208 to 277 V, 2000 W, 2 In Width, 3-3/4 In Height, Die Cast Zinc Housing Material, SPST Switch Type, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Conduit Mount, 0.6 LB/Ea
Weight per unit	0.6000 (lbs/each)
Product Category	Lighting Photocells

Features

supply voltage	120-277 VAC
Timing Range	2 Minutes

Dimensions and Weight

Size	.500 Conduit Mount
------	--------------------

Descriptions

Description	120/277V 2000W SPST CONDUIT MOUNT DIE CAST ZINC
extra long description	TORK 2107 Photocontrol Stem Zinc 27

Manufacturer Information

GTIN	00786261600318
UPC	786261600318

Taxonomies, Classifications, and Categories

Type	Die Cast Zinc Photocontrol
------	----------------------------

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Parking Lot-Building Perimeter-Outdoor Signage Lighting
Enclosure	Zinc Diecast
environmental conditions	-40 to + 140 F
Frequency Rating	50-60 Hz
Mounting	Conduit Mount
Operating Temperature	-40 to + 140 F
standard	UL-CSA