

- Frosted glass supported by Polished Chrome rings
- Damp location rated



2132FTPC
Bath Vanity

B



2131FTPC
Bath Vanity

A



2133FTPC
Bath Vanity

C



2134FTPC
Bath Vanity

D

ITEM#	LAMPING	DIMENSION	Additional Info.
A 2131	1 x 60W MB, Incan.	4.75"W x 9.5"H x 6.25"Ext.	
B 2132	2 x 60W MB, Incan.	14"W x 9.5"H x 6.25"Ext.	
C 2133	3 x 60W MB, Incan.	22.5"W x 9.5"H x 6.25"Ext.	
D 2134	4 x 60W MB, Incan.	30.75"W x 9.5"H x 6.25"Ext.	

Finish: Frosted glass (FT) Polished Chrome (PC)

FINISH

AB	Antique Brass	MS	Matte Silver
ABZ	Architectural Bronze	NA	Natural
ACP	Antique Copper	NAB	Natural Aged Brass
AE	Adobe	OB	Oriental Bronze
AL	Brushed Aluminum	OI	Oil Rubbed Bronze
AP	Antique Pecan	PB	Polished Brass
AR	Anthracite	PC	Polished Chrome
AT	Artesian Bronze	PD	Platinum Dusk
ATR	Antique Terra	PL	Platinum
BK	Black	PN	Polished Nickel
BRB	Burnished Bronze	RG	Rose Gold
BRZ	Anodized Bronze	RP	Rust Patina
BS	Black Smith	RT	Russet
BU	Burnished	RUB	Rustic Bronze
BUB	Burnished Brass	SBR	Satin Brass
BW	Barn Wood	SE	Sienna
BY	Bay	SG	Silver Gold
BZ	Bronze	SL	Silver Leaf
BZF	Bronze Fusion	SM	Silver Mist
BZGT	Bronze Gilt	SN	Satin Nickel
CH	Chocolate	SS	Satin Silver
CR	Clear Ribbed	SST	Stainless Steel
CST	Claystone	SV	Silver
DBZ	Dark Bronze	SW	Senora Wood
DSN	Dask Satin Nickel	TBZ	Textured Bronze
FG	French Gold	TE	Texture Ebony
GB	Gold Bronze	TR	Topaz Ribbed
GBK	Galaxy Black	TXB	Textured Black
GBZ	Galaxy Bronze	WBR	Weathered Brass
GL	Gold Leaf	WE	Wenge
GLD	Gold	WT	White
GO	Golden Bronze	WWD	Weathered Wood
GS	Golden Silver	WZ	Weathered Zinc
IO	Iron Ore		
LB	Luster Bronze		
MB	Metallic Bronze		

GLASS STYLES

BC	Beveled Crystal	LA	Lace
BG	Bubble Glass	LT	Latte
CD	Seedy	MC	Mocha Cloud
CG	Cognac	MO	Mocha
CI	Clear Ice	MSC	Mesh Screen
CL	Clear	PL	Pellet
CON	Constellation	RR	Plastra Rolled
CR	Clear Ribbed	SF	Snow Flake
CRY	Crystalline	SH	Scotch Crystal
CW	Clear Wave	SW	Satin White
CY	Crystal	TBG	Topaz Bubble Glass
FC	Frosted Seedy	WF	Weathered Frost
FG	Fog	WG	Waterglass
FS	Frosted Seedy	WP	Wisp
FT	Frosted	WS	Wilshire
GF	Golden Frost	WT	White
HO	Honey		
IB	Iceburg		
IC	Ice		
JC	Flambe Crystal		

SHADES

AF	Amber Fiber	NA	Natural
CG	Cognac	OM	Oatmeal
CH	Chocolate	RB	Rustic Beige
CI	Country Iron	SS	Silver Sheer
CP	Copper	TS	Tan Sheer
CS	Chocolate Sheer	UD	Uddo
FR	Ferrous	WA	White Wafer
GS	Golden Sheen	WF	White Fiber
GY	Grey	WL	White Linen
HP	Hemp	WT	White
JV	Jave		
LN	Linen		