



# M18™ RADIUS™ CPT Site Light wONE-Key (Twistlock)

2147-20



## What's Included

- (1) M18™ RADIUS™ CPT Site Light wONE-Key (Twistlock) (2147-20)
- (1) Security Cable

## Where to Buy

- Shop Online
- Find Local


The Industry's first Task, Area, and Overhead Light. The new M18™ Radius™ LED Compact Site Light with One Key(TM) (TwistLock) is the World's first high output cordless site light on the market, and has the ability to provide light in task, area, and overhead applications. With 4,400 lumens for full workspace coverage, the M18™ Radius™ LED Compact Site Light provides enough light to illuminate large work areas, and can be turned down to as low as 1,000 lumens for working in confined areas. A high impact polycarbonate lens, and IP54 ingress protection allows it to live in the toughest conditions. The combination of these technologies offers professionals the highest quality LED lighting solution, on or off the jobsite.

## Features

- 4,400 Lumens for Full Workspace Coverage
- High Impact Polycarbonate Lens
- AC In and Out: String up to 10 together
- Protected AC Plugs
- Self-Centering Hang Hook
- 180 and 360 Electronic Light Control
- Low Battery indicator
- Set Light Remotely from 100 ft
- Optimize Brightness and Runtime
- Program Automatic Schedule
- Integrated Tool Tracking & Security

## Specifications

<b>Voltage</b>	18V
<b>Length</b>	11.25"
<b>Weight</b>	12.05 lbs
<b>Height</b>	11.25"
<b>Width</b>	9.25"
<b>Compatible Batteries</b>	Compatible with all M18 Battery Packs
<b>Compatible Chargers</b>	Compatible with all M18 Chargers





# M18™ RADIUS™ CPT Site Light wONE-Key (Twistlock)



2147-20



## What's Included

- (1) M18™ RADIUS™ CPT Site Light wONE-Key (Twistlock) (2147-20)
- (1) Security Cable

## Where to Buy

-  Shop Online
-  Find Local

The Industry's first Task, Area, and Overhead Light. The new M18™ Radius™ LED Compact Site Light with One Key(TM) (TwistLock) is the World's first high output cordless site light on the market, and has the ability to provide light in task, area, and overhead applications. With 4,400 lumens for full workspace coverage, the M18™ Radius™ LED Compact Site Light provides enough light to illuminate large work areas, and can be turned down to as low as 1,000 lumens for working in confined areas. A high impact polycarbonate lens, and IP54 ingress protection allows it to live in the toughest conditions. The combination of these technologies offers professionals the highest quality LED lighting solution, on or off the jobsite.

## Features

- 4,400 Lumens for Full Workspace Coverage
- High Impact Polycarbonate Lens
- AC In and Out: String up to 10 together
- Protected AC Plugs
- Self-Centering Hang Hook
- 180 and 360 Electronic Light Control
- Low Battery indicator
- Set Light Remotely from 100 ft
- Optimize Brightness and Runtime
- Program Automatic Schedule
- Integrated Tool Tracking & Security

## Specifications

<b>Voltage</b>	18V
<b>Length</b>	11.25"
<b>Weight</b>	12.05 lbs
<b>Height</b>	11.25"
<b>Width</b>	9.25"
<b>Compatible Batteries</b>	Compatible with all M18 Battery Packs
<b>Compatible Chargers</b>	Compatible with all M18 Chargers

