

Ordering Information for Insulating and Splicing Tapes

Product Number	UPC (054007-)	Size	Inner Unit Pack	Case Qty.
Scotch® 130C Linerless Rubber Splicing Tape				
130C	41717	3/4" x 30' (19 mm x 9,1 m)	1/box	24 rolls
130C	41751	1" x 10' (25 mm x 3 m)	1/box	24 rolls
130C	41752	1" x 15' (25 mm x 4,6 m)	1/box	24 rolls
130C	41753	1" x 30' (25 mm x 9,1 m)	1/box	24 rolls
130C	41718	1-1/2" x 30' (38 mm x 9,1 m)	1/box	12 rolls
130C	41754	2" x 30' (51 mm x 9,1 m)	1/box	12 rolls
Scotch® 13 Electrical Semiconducting Tape				
13	15017	3/4" x 15' (19 mm x 4,57 m)	1/box, 10/ctn	50 rolls
Scotch® 23 Rubber Splicing Tape				
23	15025	3/4" x 30' (19 mm x 9,1 m)	1/box	50 rolls
23	13061	1" x 20' (25 mm x 6,1 m)	1/box	50 rolls
23	00059	1" x 30' (25 mm x 9,1 m)	1/box	50 rolls
23	11214	1-1/2" x 30' (38 mm x 9,1 m)	1/box, 10/ctn	50 rolls
23	15033	2" x 30' (51 mm x 9,1 m)	1/box, 10/ctn	50 rolls
Note: Other widths and lengths available upon request.				
Scotch® 24 Electrical Shielding Tape				
24	15058	1" x 100' (25 mm x 30,5 m)	1/box, 10/ctn	50 rolls
24	15041	1" x 15' (25 mm x 4,6 m)	1/box, 10/ctn	50 rolls
Scotch® 25 Electrical Grounding Braid				
25	11602	1/2" x 15' (13 mm x 4,6 m)	1/box	1 roll
Scotch® 70 Self-Fusing Silicone Rubber Electrical Tape				
70	15603	1" x 30' (25 mm x 9,1 m)	1/box, 10/ctn	50 rolls
Scotch® 77 Fire and Electric Arc Proofing Tape				
77	42007	1-1/2" x 20' (38 mm x 6,1 m)	1/bag	10 rolls
77	42006	3" x 20' (76 mm x 6,1 m)	1/bag	10 rolls
3M™ 2242 Linerless Electrical Rubber Tape				
2242	06165	3/4" x 15' (19 mm x 4,6 m)	1/bag	24 rolls
2242	41323	1-1/2" x 15' (38 mm x 4,6 m)	1/bag	12 rolls
2242	43251	2" x 15' (51 mm x 4,6 m)	N/A	8 rolls
Scotchfil™ Electrical Insulation Putty				
	41750	1-1/2" x 60" (38 mm x 1,53 m)	4/cello, 12 rolls	50 rolls
Scotch® 2510 Varnished Cambric Tape				
2510	41720	3/4" x 60' (19 mm x 18,3 m)	1/box	20 rolls
2510	10661	3/4" x 36 yd. (19 mm x 33 m)	bulk	48 rolls
2510	10687	1" x 36 yd. (25 mm x 33 m)	bulk	36 rolls
2510	10703	1-1/2" x 36 yd. (38 mm x 33 m)	bulk	24 rolls
2510	10711	2" x 36 yd. (51 mm x 33 m)	bulk	16 rolls
2510	15751	36" x 25 yd. (914,4 mm x 22,9 m)	N/A	1 roll
Scotch® 2520 Varnished Cambric Tape				
2520	04836	3/4" x 60' (19 mm x 18,3 m)	1/box	20 rolls
2520	04835	3/4" x 36 yd. (19 mm x 33 m)	bulk	48 rolls
2520	04833	1" x 36 yd. (25 mm x 33 m)	bulk	36 rolls
2520	04832	1-1/2" x 36 yd. (38 mm x 33 m)	bulk	24 rolls
2520	04834	2" x 36 yd. (51 mm x 33 m)	bulk	16 rolls
Temflex™ 2155 Rubber Splicing Tape				
2155 (replaces 2150)	50348	3/4" x 22' (19 mm x 6,7 m)	bulk	50 rolls
2155 (replaces 2150)	50349	1-1/2" x 22' (38 mm x 6,7 m)	bulk	50 rolls