



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 22282X10FT Scotch Rubber Mastic Tape, 2" X 10', BK *Minnesota Mining (3M)*

Catalog Number	22282X10FT
Manufacturer	Minnesota Mining (3M)
Description	Scotch® Tape 2228 Is A 65 Mil Thick, Premium Grade, Highly Conformable Tape Used to Insulate, Pad and Seal Bus Bar and Splice Connections. It Withstands Temperatures Up to 194 °F (90 °C).
Weight per unit	0.0921 (lbs/each)
Product Category	Markers & Marking Tapes - Tape

### Descriptions

Description	SCOTCH RUBBER MASTIC TAPE, 2" X 10', BK
extra long description	3M 7000005986 Scotch® Rubber Mastic
Features	Scotch® Tape 2228 is moisture resistant and has an aggressive, temperature stable mastic adhesive that offers excellent adherence. This tape features an ethylene propylene rubber backing and optimally resists against UV rays. Ideal for both indoor and weather exposed outdoor applications, this tape is designed for all your moisture sealing and electrical insulating applications. RoHS 2011/65/EU Compliant.
Long Description	Scotch® Tape 2228 is a 65 mil thick, premium grade, highly conformable tape used to insulate, pad and seal bus bar and splice connections. It withstands temperatures up to 194 °F (90 °C).
Product Type	Scotch® Rubber Mastic Tape 2228

### Manufacturer Information

Brand	Minnesota Mining (3M)
GTIN	00054007096566
Manufacturers Part Number	2228-2X10FT
UPC	054007096566

### Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Sealing and Insulating Mastic

### Packaging

Carton	10
Weight Per each	0.0921