



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24121012 Type 12 SGL-Door Enc, 24X12X10

Cooper B-Line/Cable Tray

Catalog Number	24121012
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 24" Height, 10" Length, 12" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	25.3 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	10.0000 IN X 12.0000 IN X 24.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	12.00 In Width X 10.00 In Depth X 24.00 In Height
------	---

Descriptions

Description	TYPE 12 SGL-DOOR ENC, 24X12X10
extra long description	B-LINE 241210-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 24" height, 10" length, 12" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 24X12X10
Special Features	Plated door clamps

Manufacturer Information

Brand	Cooper B-Line/Cable Tray
Manufacturers Part Number	241210-12

Taxonomies, Classifications, and Categories

Type	Type 12 panel enclosures
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	9999
Weight Per each	25.3

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Critical Power Other IT and Datacom - IT and Datacomm - Other Datacenters - IT Space: CI and Hyper Converged Commercial / Institutional Buildings / Str
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	CSA C22.2., NEMA, UL 508A