



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



248520 M12 Fuel 1/4" Right Angle Die Grinder

Milwaukee Electric Tool

Catalog Number	248520
Manufacturer	Milwaukee Electric Tool
Description	The M12 Fuel™ Right Angle Die Grinder Is The First Cordless Right Angle Die Grinder That Delivers The Size and Performance Professional Service Mechanics Demand. This Tool Offers Up to .3 HP Performance, Best-In-Class Size to Help Fit In Tight Places, and Offers Greater Mobility and Access. A 4-Mode RPM Control and Responsive Variable Speed Trigger Allow Users Unmatched Control.
Weight per unit	1.8 (lbs/each)
Product Category	Tools & Testers

Features

arbor size	0.25
Battery Size	12 Volt
Battery Voltage	12
Handle Type	Straight

Material, Color, and Finish

Housing Material	Reinforced Nylon
------------------	------------------

Descriptions

Description	M12 FUEL 1/4" RIGHT ANGLE DIE GRINDER
extra long description	MILW 2485-20 Right Angle Die Grinde
Long Description	The M12 FUEL™ right angle die grinder is the first cordless right angle die grinder that delivers the size and performance professional service mechanics demand. This tool offers up to .3 HP performance, best-in-class size to help fit in tight places, and offers greater mobility and access. A 4-mode RPM control and responsive variable speed trigger allow users unmatched control.
Product Type	Right Angle Die Grinder

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242544264
Manufacturers Part Number	2485-20
UPC	045242544264

Packaging

Carton	1
Weight Per each	1.825