



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24ARSL3C3UNVMP2 2X4 Led Center Basket Trof 35K/4K/5K - 2 Pack *Cooper Lighting Solutions*

Catalog Number	24ARSL3C3UNVMP2
Manufacturer	Cooper Lighting Solutions
Description	Achieva 2X4 Selectable Lumens and CCT Troffer, Ultra Slim, 0-10V Dimming to 5% Standard With 120-277V Unv, Multi-Pack 2
Weight per unit	29.8 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.17A at 277V
Lamp Type	LED
Voltage Rating	120-227V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	2X4 LED CENTER BASKET TROF 35K/4K/5K - 2 PACK
extra long description	CLS 24ARS-L3C3-UNV-MP2 2X4 3LM 3CCT
Long Description	Achieva 2x4 Selectable Lumens and CCT Troffer, Ultra Slim, 0-10V dimming to 5% standard with 120-277V UNV, Multi-Pack 2
Product Type	2X4 3LM 3CCT Troffer 80CRI RD Unv 10V 2
Special Features	Design friendly with (3) selectable color temperatures and (3) selectable lumen packages

Manufacturer Information

Brand	METALUX
GTIN	00080083282364
Manufacturers Part Number	24ARS-L3C3-UNV-MP2
UPC	080083282364

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED

Packaging

Carton	2
Weight Per each	29.8

Uses, Certifications, and Standards

Application	lighting
Mounting standard	Surface or Recessed UL Listed;RoHS Compliant;IC Rated;Title 24 Compliant;LM79/LM80 Compliant