



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24GRLD538F1UNVL8 24grld538f1unvl835cd1u *Cooper Lighting Solutions*

Catalog Number	24GRLD538F1UNVL8
Manufacturer	Cooper Lighting Solutions
Description	GR Series Led Recessed Troffer, 2 X 4, 3800 Lumen, 3500K, 0 to 10V Dim Driver
Weight per unit	21.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.126 at (277V)
Lamp Type	LED
Material	Steel
Number of Lamps	1
Voltage Rating	120-277V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	24GRLD538F1UNVL835CD1U
extra long description	CLS 24GR-LD5-38-F1-UNV-L835-CD1-U G
Long Description	GR Series LED Recessed Troffer, 2 x 4, 3800 Lumen, 3500K, 0 to 10V Dim Driver
Product Type	GR Led Trof, 2 X 4, 3800 LM, 35K, 0-10V
Special Features	Available in 2' x 4', 2' x 2' and 1' x 4'

Manufacturer Information

Brand	METALUX
GTIN	00080083798650
Manufacturers Part Number	24GR-LD5-38-F1-UNV-L835-CD1-U
UPC	080083798650

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Recessed Static

Packaging

Carton	1
Weight Per each	21

Uses, Certifications, and Standards

Application	lighting
Mounting	Recessed
standard	cULus Listed;25 Degree C Ambient Temperature Rating