



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 24GRLD564F1UNV 24grld564f1unvl840cd1u *Cooper Lighting Solutions*

Catalog Number	24GRLD564F1UNV
Manufacturer	Cooper Lighting Solutions
Description	Grled Lensed Troffer, 120 to 277 V Ac, 0.217 A @ 277 V, 60 W, Cold Rolled Steel, Frost, White, 4000 K, 85, >60000 H Average Life, Dimmable, 6400 LM Brightness (Lumens), 47-15/16 In Length, 23-3/4 In Width, 3-1/4 In Height, 20 LB
Weight per unit	20.5 (lbs/each)
Product Category	Led Recessed Architectural & S

### Features

amperage rating	0.217 at (277V)
Lamp Type	INCANDESCENT LANDSCAPE LIGHT FIXTURE, ECLIPSE TYPE; ALUMINUM MATERIAL; 4.5 INCH W X 18.5 INCH H SIZE; TEXTURED ARCHITECTURAL BRONZE FINISH; UL (CANADA AND US), CSA, ETL (US) APPROVAL; 8 INCH IN-GROUND STAKE, 18 INCH STEM MOUNTING
Wattage	60 W

### Descriptions

Description	24GRLD564F1UNVL840CD1U
extra long description	ETNCL 24GR-LD5-64-F1-UNV-L840-CD1-U

### Manufacturer Information

GTIN	00080083798872
sub brand	GRLED Series
UPC	080083798872

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Recessed Static

### Packaging

Carton	1
Weight Per each	20.5

### Uses, Certifications, and Standards

Mounting	Recessed
standard	UL/cUL Listed - Damp Location