

---

## 24W47 WATERTIGHT NEMA 4X/6P LOCKING PLUG

24W47 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Locking Watertight Plug, 15amp 125volt, NEMA Configuration L5-15, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Type: Plug

Features: Watertight

Number Of Poles: 2

Number Of Wires: 3

Special Features: Watertight, NEMA

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

#### DIMENSIONS

Diameter (US): 1.63"

Length (US): 2.68"

#### TECHNICAL INFORMATION

Amps: 15A  
Material: Rubber  
NEMA Configuration Number: L5-15  
NEMA Rating: 4X/6P  
Volts: 125V  
Volts (AC): 125

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

