



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



250QCLDC120V 250W 120V T4 DC Bayonet Clear Ess Halogen Lamp

Sylvania-Ledvance

Catalog Number	250QCLDC120V
Manufacturer	Sylvania-Ledvance
Description	Tungsten Halogen Single End Super Q Clear Finish DC Bay 250WATT 120VOLT (Ess)
Weight per unit	0.0600 (lbs/each)
Product Category	Reflector Single Ended G, PS,

Features

average life	2000
Base	BA15d Double Contact Bayonet
dimnable	Yes
Lamp Type	SINGLE END
lumens	5,000
Shape	T12
start type	Instant
Voltage	120.00 V
Voltage Rating	120
Wattage	250

Material, Color, and Finish

color rendering index (cri)	100
color temperature	2950
Finish	Clear

Descriptions

Description	250W 120V T4 DC BAYONET CLEAR ESS HALOGEN LAMP
extra long description	SYL 250Q/CL/DC(ESS)-120V/58720 250Q
Long Description	Tungsten Halogen Single End SUPER Q Clear Finish DC Bay 250Watt 120Volt (ESS)
Product Type	250QCLDC120V 12/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135587207
Manufacturers Part Number	250Q/CL/DC(ESS)-120V/58720
UPC	046135587207

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	HALOGEN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
standard	ESS