



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



252020 M12 Fuel Hackzall Reciprocating Saw - Tool Only

Milwaukee Electric Tool

Catalog Number	252020
Manufacturer	Milwaukee Electric Tool
Description	The M12 Fuel™ Hackzall® Is The Fastest Cutting and Most Powerful Saw In Its Class, Delivering Over 4X More Run-Time, Up to 70% Faster Cutting, and Up to 6X Longer Tool Life Than Competitive Saws.
Weight per unit	3.6 (lbs/each)
Product Category	Battery Driven Tools

Features

Battery Voltage	12
Stroke Length	0.625
Switch Type	Trigger

Material, Color, and Finish

Housing Material	Plastic with Rubber Overmold
------------------	------------------------------

Dimensions and Weight

Length	11
Width	2.75

Descriptions

Description	M12 FUEL HACKZALL RECIPROCATING SAW - TOOL ONLY
extra long description	MILW 2520-20 M12 FUEL™ HACKZALL® -
Features	The M12 series offers solutions that deliver portable productivity. They take on the tightest spaces and are specifically built to go anywhere. They are trade focused, system wide, lightweight with ergonomic design make portability easy, and operation faster and more productive.
Long Description	The M12 FUEL™ HACKZALL® is the fastest cutting and most powerful saw in its class, delivering over 4X more run-time, up to 70% faster cutting, and up to 6X longer tool life than competitive saws.
Product Type	M12 Fuel™ Hackzall® - Tool Only

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242318827
Manufacturers Part Number	2520-20
UPC	045242318827

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	3.645