



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



252SRTI 1" Ins Steel Emt Raintight Compression Conn *Bridgeport Fittings*

Catalog Number	252SRTI
Manufacturer	Bridgeport Fittings
Description	Compression Connector, 1 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 2 In Length, 1-17/32 In Diameter, +105 °C Operating Temperature, 0.24 LB/Ea
Weight per unit	0.2400 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Steel Raintight/Concrete-Tight Insulated
insulation	Insulated Throat
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	1
------	---

Descriptions

Description	1" INS STEEL EMT RAINLIGHT COMPRESSION CONN
extra long description	BPT 252-SRTI 1" STEEL RAINLIGHT CON

Manufacturer Information

Brand	Bridgeport
GTIN	00781747122520
UPC	781747122520

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1
------------	---

Packaging

Carton	10
Package	100
Weight Per each	0.24

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight/Raintight. Insulated Throat - 105°C. Patented
standard	cULus