



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



257DCI2 3" Diecast Emt Insulated Concrete Tight Conn *Bridgeport Fittings*

Catalog Number	257DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 Inch
Weight per unit	2.0 (lbs/each)
Product Category	Die Cast Insulated Straight CO

Features

Connector Type	Compression
insulation	Insulated Throat
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	3
------	---

Descriptions

Description	3" DIECAST EMT INSULATED CONCRETE TIGHT CONN
extra long description	BPT 257-DCI2 3" COMP. CONN. INS.
Features	Think Orange: Zinc Advantage –Error-free Performance – meets same stringent UL tests as steel. Bridgeport zinc EMT fittings set the standard for EMT.
Long Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 Inch
Product Type	3" Comp. Conn. Ins.
Special Features	Concrete-Tight

Manufacturer Information

Brand	Bridgeport
GTIN	00781747162571
Manufacturers Part Number	257-DCI2
UPC	781747162571

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	3
------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	12
Weight Per each	2

Uses, Certifications, and Standards

Application	Used to join steel EMT to box or enclosure. Concrete-tight. 2 1/2" thru 4" suitable for use with Steel EMT. Insulator rated 105°C. 2-1/2" through 4" also listed for use with Steel and Aluminum Rigid Conduit.
-------------	---

standard	cULus
----------	-------