



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 258DCI2 3-1/2" Diecast Emt Insulated Concrete Tight Conn *Bridgeport Fittings*

Catalog Number	258DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 1/2 Inch
Weight per unit	3.0 (lbs/each)
Product Category	Die Cast Insulated Straight CO

### Features

Connector Type	Compression
insulation	Insulated Throat
media	Yes

### Material, Color, and Finish

Finish	Ball burnish
--------	--------------

### Dimensions and Weight

Size	3-1/2
------	-------

### Descriptions

Description	3-1/2" DIECAST EMT INSULATED CONCRETE TIGHT CONN
extra long description	BPT 258-DCI2 3 1/2" COMP. CONN. INS
Features	Think Orange: Zinc Advantage –Error-free Performance – meets same stringent UL tests as steel. Bridgeport zinc EMT fittings set the standard for EMT.
Long Description	Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 1/2 Inch
Product Type	3 1/2" Comp. Conn. Ins.
Special Features	Concrete-Tight

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747162588
Manufacturers Part Number	258-DCI2
UPC	781747162588

### Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	CONNECTOR

### Trade Size

Trade Size	3-1/2
------------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	6
Weight Per each	3

## Uses, Certifications, and Standards

Application	Used to join steel EMT to box or enclosure. Concrete-tight. 2 1/2" thru 4" suitable for use with Steel EMT. Insulator rated 105°C. 2-1/2" through 4" also listed for use with Steel and Aluminum Rigid Conduit.
standard	cULus