




GE
Lighting

14641 - 25T61/2

GE T6.5



GENERAL CHARACTERISTICS

Lamp Type	Incandescent - Tubular
Bulb	T6.5
Base	Intermediate Screw (E17)
Filament	C-8
Bulb Finish	Clear
Rated Life	1000.0 hrs
Bulb Material	Soft glass

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	244.0
Nominal Initial Lumens per Watt	9

ELECTRICAL CHARACTERISTICS

Wattage	25.0
Voltage	130.0
Estimated Energy Cost per Year	3.01

DIMENSIONS

Maximum Overall Length (MOL)	5.5000 in(139.7 mm)
Bulb Diameter (DIA)	0.813 in(20.7 mm)

PRODUCT INFORMATION


Product Code	14641
Description	25T61/2
Standard Package	Case
Standard Package GTIN	10043168146415
Standard Package Quantity	60
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	60
UPC	043168146418



GE
Lighting

14641 - 25T61/2

GE T6.5



GENERAL CHARACTERISTICS

Lamp Type	Incandescent - Tubular
Bulb	T6.5
Base	Intermediate Screw (E17)
Filament	C-8
Bulb Finish	Clear
Rated Life	1000.0 hrs
Bulb Material	Soft glass

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	244.0
Nominal Initial Lumens per Watt	9

ELECTRICAL CHARACTERISTICS

Wattage	25.0
Voltage	130.0
Estimated Energy Cost per Year	3.01

DIMENSIONS

Maximum Overall Length (MOL)	5.5000 in(139.7 mm)
Bulb Diameter (DIA)	0.813 in(20.7 mm)

PRODUCT INFORMATION

Product Code	14641
Description	25T61/2
Standard Package	Case
Standard Package GTIN	10043168146415
Standard Package Quantity	60
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	60
UPC	043168146418