



## SPECIFICATION GRADE DECORATOR SWITCH, GRAY

2624GRY | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Four-Way, Back and Side Wire, Decorator Switch, 20 amps, 120/277 volts, Gray.

- Impact-resistant polycarb back body and frame.
- Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
- Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.
- Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.
- Terminals made of high conductivity brass and serrated for maximum wire gripping.
- Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
- Integral auto-ground clip for positive ground to metal boxes.
- Tri-drive ground, terminal, and mounting screws.
- All terminal screws backed out, ready-to-install.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Number Of Poles: 4-way  
Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 111  
CSA Standard: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

#### DIMENSIONS

Depth (US): 1.06"

Height (US): 4.2"  
Width (US): 1.3"

#### TECHNICAL INFORMATION

Amps: 20A  
Volts: 120/277VAC  
Volts (AC): 120/277

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

