



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2624GRY SW Dec 4W 20A 120/277V Grounded Gy

Pass & Seymour/Legrand

Catalog Number	2624GRY
Manufacturer	Pass & Seymour/Legrand
Description	4-Way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Weight per unit	0.2540 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Material	Polycarbonate, Thermoplastic
media	Yes
Mounting Type	Box
Poles	4-Way
Switch Type	Paddle
Voltage	120/277 V
Voltage Rating	120/277
Wattage	4
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Gray
Finish	Matte

Dimensions and Weight

Size	4.25"
------	-------

Descriptions

Description	SW DEC 4W 20A 120/277V GROUNDED GY
extra long description	P&S 2624GRY SW DEC 4W 20A 120/277V
Features	Decorator Style
Long Description	4-way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Product Type	SW Dec 4W 20A 120/277V Grounded Gy
Special Features	Impact resistant polycarb back body & frame, cushioned thermoplastic paddle , unique single rocking butterfly contact

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007539622
Manufacturers Part Number	2624-GRY
UPC	785007539622



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Decorator, Switch

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.254

Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL CSA, CULUS, UL 20