

# Heavy-Duty Decorator Spec Grade Receptacles, Side Wire, 20A, 125V, Ivory

26342I



Heavy-Duty Decorator Spec Grade Duplex  
Receptacle Side Wire 20amp 125volt Ivory



## features & benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

## specifications

**General Info**

Color: Ivory  
Type: Receptacles  
Duty: Heavy Duty  
Special Features: Side Wire  
Style: Decorator

**Listing Agencies/Third Party Information**

CSA Listing Info: No  
CUL Listing No: Yes  
cULus: No  
cURus: No  
Federal Spec: Yes  
UL Listing No: No  
UN SPS C: 39121406  
UR: No

**Dimensions**

Depth U S: 0.833"  
Height U S: 3.281"  
Width U S: 1.322"

**Technical Information**

Amps: 20 Amp  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Specification

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant