



HEAVY-DUTY DECORATOR SPEC GRADE RECEPTACLES, SIDE WIRE, 20A, 125V, RED

26342RED | [Pass & Seymour](#)

FEATURES & BENEFITS

Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 20amp 125volt Red



- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Red
Type: Receptacles
Duty: Heavy Duty
Special Features: Side Wire
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: Yes
cULus: No

cURus: No
Federal Spec: Yes
UL Listing No: No
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 0.833"
Height (US): 3.281"
Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 20A
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

