

Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Gray

26352GRY



Heavy-Duty Decorator Spec Grade Duplex
Receptacle Back & Side Wire 20amp
125volt Gray



features & benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: gray
Type: Receptacles
Duty: Heavy Duty
Special Features: Back, Side Wire
Style: Decorator

Listing Agencies/Third Party Information

CSA Standard: Yes
cUL Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 0.833"
Height U S: 3.281"
Width U S: 1.322"

Technical Information

Amps: 20 Amp
Volts: 125V
Volts A C: 125
Capacity: Duplex
Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant