



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



266RT 2-1/2" Diecast Emt Raintight Compression Coupling

Bridgeport Fittings

Catalog Number	266RT
Manufacturer	Bridgeport Fittings
Description	2-1/2" Raintight Coupling
Weight per unit	1.5 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Connector Type	Compression
media	Yes
outside diameter	3.44

Dimensions and Weight

Length	3.75
--------	------

Descriptions

Description	2-1/2" DIECAST EMT RAIN TIGHT COMPRESSION COUPLING
extra long description	BPT 266-RT 2-1/2" RAIN TIGHT CPLG
Features	Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations.
Long Description	2-1/2" Raintight Coupling
Product Type	2-1/2" Rain Tight CPLG
Special Features	With Bridgeport's newly redesigned Raintight Compression Couplings, 266-RT through 269-RT, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT.

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747142665
Manufacturers Part Number	266RT
UPC	781747142665

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	Raintight

Trade Size

Trade Size	2.5
------------	-----

Packaging

Carton	12
Weight Per each	1.525



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

These 2-1/2" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAINIGHT" clearly cast into the body. This marking helps the AHJ to precisely confirm the products intended use.

Patented

standard

cULus