

M18 FUELTM High Torque ¹/₂" Impact Wrench with Pin Detent (Tool Only)

2766-20



What's Included

(1) M18 FUEL™ High Torque ½" Impact Wrench with Pin Detent (Tool Only) (2766-20)

GUIDE

Where to Buy



The 2766 M18 FUELTM High Torque ¹/₂" Impact Wrench with Pin Detent provides a full corded replacement delivering 750ft-lbs of fastening torque and 1100ft-lbs of nut-busting torque. The industry's most compact cordless High Torque Impact wrench at 8.1" in length, this tool allows for more access in tight spaces. 4-Mode DRIVE CONTROLTM with Bolt Removal mode gives users the most control over their fasteners. Bolt Removal mode gives the user more control when removing fasteners by slowing to 750rpm once the fastener has been busted loose. This tool includes a ¹/₂" Pin Detent anvil which provides superior socket retention. A premium rubber overmold material gives you ultimate comfort during prolonged use while lasting longer against corrosive materials.

Features

- Most compact cordless High Torque Impact Wrench in its class at 8.1" in length
- Bolt removal mode provides maximum nut-busting torque to break fastener free, then slows to 750rpm for more control when removing fasteners
- REDLINK PLUSTM intelligence prevents damage to the tool and battery due to overloading or overheating
- REDLITHIUM[™] batteries deliver more work per charge and more work over the life of the battery
- Features a pin detent design for maximum socket retention
- Premium rubber overmold withstands corrosive materials and provides increased comfort when in use
- Reduced user fatigue at only 7.1lbs with battery (battery not included)
- LED light to illuminate the work area

f 🖸 G+ 🖸 🛩 🛗

Specifications

Voltage	18V
Fastening Torque	750 ft-lbs
IPM	1,150/2,100/2,400/2,400
RPM	0 to 950/1,500/1,800/1,800-750
Warranty	5 Year Limited Warranty
Drive Control	4-mode
Length	8.1"
Weight	5.5 lbs
LED Light	Yes
Tool Warranty	5 Years