
MEDIUM BASE LAMPHOLDER

276WH | [Pass & Seymour](#)



FEATURES & BENEFITS

Medium base, phenolic, one-piece keyless, 4 terminals with tri-drive screws, fits 3 1/4" and 4" boxes, with cage neck. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (US): 4.5"

TECHNICAL INFORMATION

Volts: 250V

Volts (AC): 250

Watts: 660

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No

MEDIUM BASE LAMPHOLDER

276WH | [Pass & Seymour](#)



FEATURES & BENEFITS

Medium base, phenolic, one-piece keyless, 4 terminals with tri-drive screws, fits 3 1/4" and 4" boxes, with cage neck. White.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39111803
UR: No

DIMENSIONS

Diameter (US): 4.5"

TECHNICAL INFORMATION

Volts: 250V

Volts (AC): 250

Watts: 660

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No