



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



27W75 Turnlok Conn IP67 20A 3PH 250V L1520R

Pass & Seymour/Legrand

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 27W75 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Locking Watertight Connector, 20AMP, 3 250VOLT, Nema Configuration L15-20, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated. |
| Weight per unit | 0.8300 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|------------------------------------------|
| amperage rating | 20 |
| Cord Type | 14/4 S to 10/4 S, .560" min to .775" max |
| Material | Rubber |
| Number of Wires | 4.0 |
| Phase | Three |
| Poles | 3-way |
| Voltage | 250.0 V |
| Voltage Rating | 250 |
| Wire Size | 14 - 10 AWG |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Yellow |
|-------|--------|

Descriptions

| | |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | TURNLOK CONN IP67 20A 3PH 250V L1520R |
| extra long description | P&S 27W75 TL CONN IP67 20A 3PH 250V |
| Long Description | Locking Watertight Connector, 20amp, 3 250volt, NEMA Configuration L15-20, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated. |
| Product Type | TL Conn IP67 20A 3PH 250V L1520R |
| Special Features | Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007033106 |
| Manufacturers Part Number | 27W75 |
| UPC | 785007033106 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Locking Connector |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 20.0

Packaging

Carton 1

Package 10

Weight Per each 0.83

Uses, Certifications, and Standards

Application

High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors | Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings | Ideal for washdown areas — rated wa

environmental conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

nema rating

L15-20R

standard

UL Listed, CSA Listed