



SNA Terminal Blocks
T&B Catalog Number:

029006917
 66201997016
 Active

UPC Number:
Status:
Description:

Green and yellow ground block with 6 mm spacing on a DIN 3 rail and spring clamp connection

Features

- Top entry wire connection
- Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	D 4/6.P.2L
Connection Technology	Spring Clamp
UL Wire Range (AWG)	24-10
Rated IEC Wire Range (Solid) (mm ²)	0.2 - 6
Rated IEC Wire Range (Stranded) (mm ²)	0.2 - 4

Dimension Information

L x W x H (mm)	62.5 x 6 x 38
Spacing (mm)	6
L x W x H (in)	2.46 x .238 x 1.49
Spacing (inches)	.238

Specifications

Rated UL Wire Size (AWG)	10
--------------------------	----

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.03 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com



SNA Terminal Blocks
T&B Catalog Number:

029006917
 66201997016
 Active

UPC Number:
Status:
Description:

Green and yellow ground block with 6 mm spacing on a DIN 3 rail and spring clamp connection

Features

- Top entry wire connection
- Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	D 4/6.P.2L
Connection Technology	Spring Clamp
UL Wire Range (AWG)	24-10
Rated IEC Wire Range (Solid) (mm ²)	0.2 - 6
Rated IEC Wire Range (Stranded) (mm ²)	0.2 - 4

Dimension Information

L x W x H (mm)	62.5 x 6 x 38
Spacing (mm)	6
L x W x H (in)	2.46 x .238 x 1.49
Spacing (inches)	.238

Specifications

Rated UL Wire Size (AWG)	10
--------------------------	----

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.03 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com