



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 29W74 Turnlok Conn IP67 30A 125/250V L1430R

*Pass & Seymour/Legrand*

Catalog Number	29W74
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Connector, 30AMP 125/250VOLT, Nema Configuration L14-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8150 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
Material	Rubber
Number of Wires	4.0
Phase	Single
Poles	3-way
Voltage Rating	125/250
Wire Size	12 - 6 AWG

### Material, Color, and Finish

Color	Yellow
-------	--------

### Descriptions

Description	TURNLOK CONN IP67 30A 125/250V L1430R
extra long description	P&S 29W74 TL CONN IP67 30A 125/250V
Long Description	Locking Watertight Connector, 30amp 125/250volt, NEMA Configuration L14-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	TL Conn IP67 30A 125/250V L1430R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033762
Manufacturers Part Number	29W74
UPC	785007033762

### Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Locking Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage 30.0

## Packaging

Carton 1

Package 10

Weight Per each 0.815

## Uses, Certifications, and Standards

Application High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors | Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings | Ideal for washdown areas — rated wa

environmental conditions Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

nema rating L14-30R

standard UL Listed, CSA Listed