






Atlanta, Georgia

Phone 800-521-7326

Fax 770-745-1333

www.pecofasteners.com

Bugle Head Coarse Thread Drywall Screws (Black Phosphate Finish)



Peco Catalog#	Screw Size	Threads Per Inch	Driver Size	D		A		H		R		I	
				Min Diameter	Max Diameter	Min	Max	Min	Max	Min	Max	Min	Max
See Section 1 of Peco Catalog	6	8	2	.142	.154	.315	.347	.020	.031	.176	.189	.087	.110
	7	8	2	.159	.172	.322	.355	.020	.035	.191	.206	.102	.125
	8	8	2	.163	.180	.330	.363	.020	.039	.201	.214	.112	.135
	10	8	2	.180	.210	.344	.379	.020	.045	.208	.222	.137	.142
Tolerance on Length				Up to 1" 0, +0.060	Over 1" 0, +0.100								
Material	AISI 1018 or Equivalent Steel												
Hardness	Rockwell C 44 minimum												
Heat Treatment	Quenched in liquid and then tempered by reheating to 650° Minimum												

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.