



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2EP3GX332S36IUNV Parabolic Trof 18 Cell 3 Lamp Electronic Ballast

Cooper Lighting Solutions

Catalog Number	2EP3GX332S36IUNV
Manufacturer	Cooper Lighting Solutions
Description	3 Lamp, 2'X4' Static Parabolic, 18 Cell, Semi Specular/Low Iridescent Haze 3" Louver, Cee Listed Electronic Ballast, T8
Weight per unit	27.4 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.116 at (277V)
Ballast Type	Instant Start
Lamp Type	T8 (Not Included)
Material	Steel
Number of Lamps	3
Voltage Rating	120-277V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	PARABOLIC TROF 18 CELL 3 LAMP ELECTRONIC BALLAST
extra long description	CLS 2EP3GX-332S36I-UNV-EB81-U EP3 3
Long Description	3 Lamp, 2'x4' Static Parabolic, 18 Cell, Semi Specular/Low Iridescent Haze 3" Louver, CEE Listed Electronic Ballast, T8
Product Type	EP3 3 LMP, 2'X4' Par, 18 Cell, Semi, T8
Special Features	Provided with CEE-listed energy-saving ballasts

Manufacturer Information

Brand	METALUX
GTIN	00662401012084
Manufacturers Part Number	2EP3GX-332S36I-UNV-EB81-U
UPC	662401012084

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Paralux III High Performance

Packaging

Carton	1
Weight Per each	27.3599

Uses, Certifications, and Standards

Application	lighting
Mounting	Troffer
standard	UL/cUL Listed - Damp Location