



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2GT8332A12MVOLT1 2X4 Acrylic 3 LMP T8 32W

Lithonia Lighting

Catalog Number	2GT8332A12MVOLT1
Manufacturer	Lithonia Lighting
Description	Lith 2GT8 3 32 A12 Mvolt 1/3 Geb10i
Weight per unit	20.0 (lbs/each)
Product Category	Fluorescent Recessed Architect

Features

Ballast Type	Electronic Ballast
Hardware	Yes
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	3
pallet quantity	28
Shape	Rectangular
Socket Type	Bi-pin: Single
Voltage Rating	120 to 277
Warranty	1
Wattage	96

Material, Color, and Finish

Color	White
Finish	Gloss
Lens Color	Clear
Lens Material	Acrylic
Style	Traditional

Dimensions and Weight

Height	3.5
Length	48.5
Width	24.0000

Descriptions

Description	2X4 ACRYLIC 3 LMP T8 32W
Long Description	LITH 2GT8 3 32 A12 MVOLT 1/3 GEB10I
Product Type	Troffer

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00784231139479
Manufacturers Part Number	2GT8 3 32 A12 MVOLT 1/3 GEB10I
UPC	784231139479



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Troffer

Trade Size

aperture size	2x4
---------------	-----

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	19
Weight Per each	20

Uses, Certifications, and Standards

Application	Education, Offices & Banks, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	UL