



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2GT8332A12MVOLT1 2X4 Acrylic 3 LMP T8 32W

*Lithonia Lighting - Acuity*

Catalog Number	2GT8332A12MVOLT1
Manufacturer	Lithonia Lighting - Acuity
Description	Lith 2GT8 3 32 A12 Mvolt 1/3 Geb10i
Weight per unit	20.0 (lbs/each)
Product Category	Fluorescent Recessed Architect

### Features

Ballast Type	Electronic Ballast
Hardware	Yes
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	3
pallet quantity	28
Shape	Rectangular
Socket Type	Bi-pin: Single
Voltage Rating	120 to 277
Warranty	1
Wattage	96

### Material, Color, and Finish

Color	White
Finish	Gloss
Lens Color	Clear
Lens Material	Acrylic
Style	Traditional

### Dimensions and Weight

Height	3.5
Length	48.5
Width	24.0000

### Descriptions

Description	2X4 ACRYLIC 3 LMP T8 32W
Long Description	LITH 2GT8 3 32 A12 MVOLT 1/3 GEB10I
Product Type	Troffer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00784231139479
Manufacturers Part Number	2GT8 3 32 A12 MVOLT 1/3 GEB10I
UPC	784231139479

## Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Troffer

## Trade Size

aperture size	2x4
---------------	-----

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Weight	19
Weight Per each	20

## Uses, Certifications, and Standards

Application	Education,Offices & Banks,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	UL