



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2GTL44400LMLP840 2X4 Led Trof 40K 4429LM

Lithonia Lighting - Acuity

Catalog Number	2GTL44400LMLP840
Manufacturer	Lithonia Lighting - Acuity
Description	Lith 2GTL4 4400LM LP840 2X4 Led Rec
Weight per unit	19.7 (lbs/each)
Product Category	Lighting Accessories

Features

average life	50,000
dimensions	48 x 23.75 x 3.25
dimmable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	4400 LM
Material	Steel
Maximum Operating Temperature	25
pallet quantity	28
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	5
Wattage	35

Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	4000
Finish	Matte
Lens Color	Clear
Lens Material	Acrylic
Style	Traditional

Dimensions and Weight

Height	3.25
Length	48
Width	23.75

Descriptions

Description	2X4 LED TROF 40K 4429LM
Features	Contractor Select
Long Description	LITH 2GTL4 4400LM LP840 2x4 LED Rec
Product Type	Troffer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00889804706956
Manufacturers Part Number	2GTL4 4400LM LP840
UPC	889804706956

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Troffer

Trade Size

aperture size	2x4
---------------	-----

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	17.95
Weight Per each	19.65

Uses, Certifications, and Standards

Application	Education,Offices & Banks,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSADLC Standard