



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30059 I-Temp Wire-Nut Wire Conn, 59B Black, 100/Box

Ideal

Catalog Number	30059
Manufacturer	Ideal
Description	Ideal, Wire Connector, Wire-Nut, High Temperature Twist-On, Number Of Conductors: 1 to 6, Conductor Range: 22 - 12 Awg, Min 2 - 20, Max 3-14, Color: Black, Material: Thermoplastic Polyester, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-0 Flame-Retardant Shell Rated At 150 Deg C (302 F), Model Number: 59B, Width: 31/64 In, Height: 1-1/16 In
Weight per unit	0.7000 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	THERMOPLASTIC POLYESTER
Voltage Rating	600

Material, Color, and Finish

Color	Black
-------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	I-TEMP WIRE-NUT WIRE CONN, 59B BLACK, 100/BOX
extra long description	IDEAL 30-059 WIRENUT 59B BLK 100PC
Features	The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame
Long Description	IDEAL, Wire Connector, Wire-Nut, High Temperature Twist-On, Number Of Conductors: 1 to 6, Conductor Range: 22 - 12 AWG, Min 2 - 20, MAX 3-14, Color: Black, Material: THERMOPLASTIC POLYESTER, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-0 Flame-Retardant Shell Rated At 150 DEG C (302 F), Model Number: 59B, Width: 31/64 IN, Height: 1-1/16 IN
Product Type	Wirenut 59B BLK 100PC BX
Special Features	Deep Skirt Helps Protect Against Flash-Over;Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time;Height: 1-1/16 IN;Model Number: 59B;No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation;Reusable For Easy Circuit Changes And Additions;Tough, UL94V-0 Flame-Retardant Shell Rated At 150 Degree C (302 Degree F);UL Listed To 486C And CSA Certified To C22.2 #188;Width: 31/64 IN

Manufacturer Information

Brand	Ideal
GTIN	00783250300594
Manufacturers Part Number	30-059
UPC	783250300594

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	High Temperature Twist-On

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per each	0.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Insulating or Joining 2 or more conductors in conditions where extreme heat buildup occurs such as high wattage fixtures and signs.

environmental conditions

Tough, UL 94V-0 Flame-Retardant Shell Rated At 150 DEG C (302 F)

standard

CSA Certified to C22.2 #188, UL Listed to 486C