



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30076 Wiretwist Wire Connector, WT6 Red, 100/Box

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 30076  |
| Manufacturer     | Ideal  |
| Description      | Ideal, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Conductor Range: 18 - 12 Awg, Min 2-18 Max 4-14 W/ 1-18, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Model Number: 76B, Flammability Rating: UI 94V-2 |
| Weight per unit  | 0.9100 (lbs/each)  |
| Product Category | Electrical Fixture Conn ( Nuts   |

### Features

|                |                               |
|----------------|-------------------------------|
| Material       | Flame-retardant Polypropelene |
| Voltage Rating | 600                           |

### Material, Color, and Finish

|       |     |
|-------|-----|
| Color | Red |
|-------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | WIRETWIST WIRE CONNECTOR, WT6 RED, 100/BOX   |
| extra long description | IDEAL 30-076 WIRENUT 76B RED, 100 B  |
| Features               | The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame     |
| Long Description       | IDEAL, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Conductor Range: 18 - 12 AWG, Min 2-18 MAX 4-14 w/ 1-18, Material: Flame-retardant polypropelene, Color: Red, Voltage Rating: 600 V, Model Number: 76B, Flammability Rating: UL 94V-2   |
| Product Type           | Wirenut 76B Red, 100 BX  |
| Special Features       | Comply With Federal Specification W-S-610E; Deep Skirt Helps Protect Against Flash-Over; Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time; Flammability Rating: UL 94V-2; Model Number: 76B; No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation; Reusable For Easy Circuit Changes And Additions; Tough, UL94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F); UL Listed To 486C And CSA Certified To C22.2 #188 |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250300761 |
| Manufacturers Part Number | 30-076         |
| UPC                       | 783250300761   |

## Taxonomies, Classifications, and Categories

|                      |           |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type                 | Twist-On  |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 100  |
| Package         | 1000 |
| Weight Per each | 0.91 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Insulating or Joining 2 or more conductors   |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)                             |
| standard                 | CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E |